

Proof of intrinsic safety

For intrinsically safe circuits with a supply.

device:

Jellox Analog xx

associated equipment:

Manufacturer	Type	Device	EU type examination certificate	ATEX marking
Microtronics	D012-x1***2***05	Rugged GW Analog	SIQ 24 ATEX 212 X	<Ex> II 2G Ex ib IIB T3 Gb

max. output voltage	Uo [V]=	25,6
max. output current	Io [A]=	0,082
max. output power	Po [W]=	0,523
max. external capacity	Co [nF]=	310
max. external inductance	Lo [μH]=	1000

intrinsically safe equipment:

Manufacturer	Type	Device	EU type examination certificate	ATEX marking
Keller	23SYEi; 23YEi; 23YMEi; 25YEi; 26YEi; 26YMEi; PT-25YEi	Pressure & Temperature transmitter	IBExU10ATEX1124X	<Ex> II 1G Ex ia IIC T6-T4 Ga <Ex> II 1G Ex ia IIC T4 Ga

max. input voltage	Ui [V]=	30	for max. +65°C Tamb
max. input current	Ii [A]=	0,2	
max. input power	Pi [W]=	1,1	
max. internal capacity	Ci [nF]=	0	
max. internal inductance	Li [μH]=	0	

cable + pressure compensation element:

Manufacturer	Type	length [m]
Lapp	Ölflex EB CY 7x0,75	
		270

cable capacitance [nF/m]	0,98
cable inductance [μH/m]:	3,64

resulting cable capacitance	Cc [nF]=	264,6
resulting cable inductance	Lc [μH]=	982,8

safety-related values of the interconnection:

D012-x1***2***05		23SYEi; 23YEi; 23YMEi; 25YEi; 26YEi; 26YMEi; PT-25YEi		Intrinsic safety fulfilled
25,6	Uo ≤ Ui	30	V	YES
0,082	Io ≤ Ii	0,2	A	YES
0,523	Po ≤ Pi	1,1	P	YES
310	Co ≥ Ci + Cc	264,6	nF / IIB	YES
1000	Lo ≥ Li + Lc	982,8	μH / IIB	YES

For use in EPL
"Gb" (category
2G) and group
IIB

Special conditions in the type examination certificate or in the manual of the associated / intrinsically safe equipment must be observed.
The proof of intrinsic safety is based on the safety-related maximum values. These were taken from the manual or the EC type examination certificates for the equipment.

Configuration recommendation:

The recommendation refers to the configuration of your Jellox product. You can make the settings in the platform.
Please refer to the table at <https://support.microtronics.com/jellox-analog/compatible-sensors> for the configuration recommendation.



The recommendation refers to the configuration of your Jellox product. You can make the settings in the platform.

Document revision

version	date	name	change	reason
01v000	14.05.2025	AZ	all	building document

Release

number	date	name	activity	signature
1	14.05.2025	AZ	created	
2			approved	